


DYNOJET RESEARCH
CRYSTAL AUTO Co.LTD., 242-0001 2-11-8simoturuma yamato-city kanagawa japan



RunFile_013.drf - 2013/12/16 16:18:11 測定方法: RO Run Conditions: 23.67 °C, 1011.27 mBars, 湿度: 13%, SAE: 0.98
07 y FLHX
Max Power = 74.37 Max Torque = 11.82
T-MAX (CA SPL Map) MS 2in2EX KerKer S/On T-D SE HF A/C

RunFile_001.drf - 2013/12/16 15:16:35 測定方法: RO Run Conditions: 13.43 °C, 1008.98 mBars, 湿度: 24%, SAE: 0.96
07 y FLHX
Max Power = 67.73 Max Torque = 10.98
T-MAX (Base Map) MS 2in2EX KerKer S/On T-D SE HF A/C